

Smart Precision Cooling for Data Centers

The nVent SCHROFF RackChiller In-Row 45 chilled water cooler is designed to manage the critical cooling requirements of server and networking racks. The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP or third party racks. The cooler comes with perforated front and rear doors. This allows seamless integration into rows of racks with hot or cold aisle containment. The integrated fans move the warm exhaust air from the hot aisle through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold aisle towards the equipment. The units can be scaled optimally to suit individual packaging density and redundancy requirements.

FEATURES

- Fans, power supplies, controller and control valve all are hot-swappable.
- 7" high resolution touch screen interface.
- Integrated casters and levelling feet for simple reconfiguration of rows.
- Hydraulic connection and cabling through top or bottom panel.
- Automatic fan speed and valve opening control.
- Standard Dimensions: 300W / 2000H. Version in 1000D and 1200D available; other dimensions upon request.

BENEFITS

- Ideal for hot Aisle Containment.
- Maximum availability and quick repair.
- Designed for efficient operation at increased facility water temperatures.
- Combination with direct to chip liquid cooling.
- Modular standard - easy to adapt to individual requirements.
- Minimal planning outlay / short setup time.
- Minimum changes between In-Row and LHX (In-Rack) design - simplifies planning, layout and specification.



RackChiller In-Row 45

TECHNICAL INFORMATION



COOLING PERFORMANCE 44KW*

- Coolant: treated water with up to 35% glycol.
- Coolant Flow: max. 6 m³/h / 100 l/min.
- Coolant Head Loss: 100 kPa @ 80 l/min.
- Air Flow: max. 6500 m³/h free blowing.
- Cooling performance: 44 kW.
- Noise emission: 100 dB(A) with closed doors.



SPECIFICATION

Mechanical

- Height: 2000 mm / 42RU
- Width: 300 mm.
- Depth: 1000 or 1200 mm.
- Pipe Connection: 1" BSPP flat gasket or Quick Disconnect Couplings.

Electrical

- Power Requirement: 1~ 195-277 VAC, 50/60 Hz.
- Power Consumption: 1750 W.



MONITORING

- Valve position (adjustable via cold air temperature)
- Fan speed (adjustable via hot air temperature)
- Return water temperature
- Fan-function display
- Local alarm display
- User-defined preventative maintenance alarms
- Alarm log
- SNMP and Modbus interface



	Operating Point 1	Operating Point 2	Operating Point 3
Coolant Supply [°C]	14	20	24
Coolant Return [°C]	22.7	23	26.6
Coolant Flow [m ³ /h]	4.6	6	6
Air Supply (to servers) [°C]	24	24	28
Air Return (from servers) [°C]	45	45	45
Air Flow [m ³ /h]	6700	3000	3300
Cooling Performance [kW]	46	21	18
Coolant Pressure Drop [kPa]	100	160	160



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER