

FIRE-RATED WIRING SYSTEMS (CANADA) MINERAL INSULATED (MI) CABLE

This specification is dated 06/01/2022 and supersedes all previous versions.

For detailed design information, please contact your local representative, our website at nVent.com/PRYOTENAX or nVent Thermal Technical Support 800-545-6258.

PART 1 GENERAL

1.1. SUMMARY

- A. Furnish and install a complete CSA certified wiring system consisting of specified wiring cable, components, and accessories listed specifically for use with the system.

1.2. REFERENCES

- A. Reference Standards
 - 1. C22.1 Canadian Electrical Code, Part I
 - 2. ULC-S139
 - 3. CSA C22.2#124
 - 4. ULC Fire Resistance Directory

1.3. SUBMITTALS

- A. Provide product data for each cable type.
- B. Provide manufacturer's Installation Instructions: Indicate application conditions and limitations of use stipulated by product testing agency specified under Regulatory Requirements.

1.4. QUALIFICATIONS

- A. Supplier: Company specializing in manufacturing products specified in Section 16, Electrical.
- B. Supplier to have more than 30 years' experience in manufacturing products in Canada
- C. Supplier to have more than 30 million feet of product installed in Canada

1.5. REGULATORY REQUIREMENTS

- A. Conform to requirements of Canadian Electrical Code, Part I.
- B. Conform to requirements of the System Listing in the ULC Fire Resistance Director
- C. Furnish products certified by CSA as suitable for the purpose specified.

1.6. WARRANTY

- A. Manufacturer's Warranty: Provide Owner a product warranty for fire-rated wiring products described below.
 - 1. Contractor must complete insulation resistance testing prior to Commissioning and maintain records of test results.
 - 2. Warranty Period for Wiring Cable: Lifetime from date of Sale.
 - 3. Warranty information must be published on manufacturer's website.

PART 2 PRODUCTS

2.1. FIRE-RATED WIRING CABLE

- A. 2-hour fire-rated Mineral Insulated (nVent PYROTENAX MI) cables shall be acceptable.
- B. The wiring cable and splices and tees shall be listed in the ULC Fire Resistance Directory.
- C. Mineral Insulated wiring Type MI cable shall have:
 - 1. Description: C22.1-02 Canadian Electrical Code, Part I Type MI
 - 2. Conductor: solid high conductivity copper
 - 3. Insulation Voltage Rating: 600 volts
 - 4. Cable Temperature Rating: 90 degrees C
 - 5. Termination Temperature Rating: 90 degrees C
 - 6. Insulation Material: magnesium oxide.
 - 7. Sheath Material: seamless soft-drawn copper
 - 8. Fire Rating: complete cable system shall have a 2-hour fire rating as listed and classified by Underwriters Laboratories of Canada

2.2. COMPONENTS

- A. Mineral Insulated cable components shall be cCSAus Certified.
- B. Mineral Insulated cable terminations shall consist of nVent:
 - 1. nVent PYROTENAX Model PyroPak (Installation Sheet H58872) or
 - 2. nVent PYROTENAX Model QuickTerm Termination (Installation Sheet H58264 or H58290) System Startup

PART 3 EXECUTION

3.1. EXAMINATION

- A. Verify that the factory installed temporary end seals are intact.
- B. Verify that no moisture has entered cable insulation.

3.2. STORAGE

- A. Cables shall be shipped from the manufacturer with ends sealed against moisture.

- B. Protect the exposed cable ends with shrinkable, molded polyolefin end caps or other suitable means such as standard conduit sealing compound and PVC tape.
- C. Cable shall be stored in a clean dry location.

3.3. HANDLING

- A. Cable shall be uncoiled by rolling or rotating supply reel.
- B. Take precautions necessary to prevent damage to cable from contact with sharp objects, such as when pulled over foreign material on sheaves.

3.4. INSTALLATION

- A. The wiring cable shall be installed according to the manufacturer's recommendations, the instructions in the Installation Specification or Manual and the requirements of the UL Fire resistance Directory listing.

3.5. FIELD QUALITY CONTROL

- A. Inspect cable for physical damage and proper connection.
- B. Measure tightness of any bolted connections and compare torque measurements with manufacturer's recommended values.
- C. Verify continuity of each conductor.
- D. Prior to energizing cables, measure insulation resistance of each cable. Tabulate and submit for approval.
- E. Provide certification from cable manufacturer that installation is in accordance with their requirements.

END OF SECTION