

RTD4AL-EP




RAYCHEM

CONNECT AND PROTECT

RTD Temperature Sensor for Temperature Measurement Up To 900°F (482°C)

PRODUCT OVERVIEW



The nVent RAYCHEM RTD4AL-EP is a three-wire platinum RTD (resistance-temperature detector) typically used with monitoring and control systems that require accurate temperature control. The RTD4AL-EP is epoxy coated to provide added corrosion resistance. The RTD4AL-EP kit can be used with a wide variety of nVent RAYCHEM monitoring and control systems.

SPECIFICATIONS

Sensor housing & cap	Epoxy Coated Aluminum A380; TYPE 4X
Sensor sheath	Epoxy Coated 316 Stainless Steel
Range	-100°F to 900°F (-73°C to 482°C) maximum
Accuracy	±1°F (0.5°C) at 32°F (0°C)
Resistance	100 ohms at 0°C $\alpha = 0.00385$ ohms/ohm/°C
Connection	3/4-in (19 mm) NPT conduit hub Note: The length of RTD extension wires is determined by the wire gauge used. To reduce the likelihood that electrical noise will affect temperature measurement, keep RTD extension wires as short as possible. Use shielded instrument cable such as RAYCHEM MONI-RTD-WIRE (22 AWG, PVC insulation, -30°F to 140°F, -20°C to 60°C) or Belden 83553 (22 AWG, FEP insulation, -95°F to 395°F, -70°C to 200°C).

ADDITIONAL MATERIALS REQUIRED

Pipe strap, conduit, 16–22 AWG shielded instrument cable

KIT CONTENTS

One RTD temperature sensor

APPROVALS

The RTD4AL-EP is CSA certified to U.S. and Canadian standards.



Class I, Div. 2, Groups A, B, C, D
Class II, Div. 2, Groups F, G

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

info@nVent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER