


RTD TEMPERATURE SENSOR FOR TEMPERATURE MEASUREMENT UP TO 900°F (482°C) IN DIVISION 1 LOCATIONS



PRODUCT OVERVIEW

The RTD7AL temperature sensor is a three-wire platinum RTD (resistance-temperature detector) typically used with monitoring and control systems when accurate temperature control is required. The sensor is explosion-proof and approved for Division 1 hazardous locations. The RTD7AL can be used with a wide variety of nVent RAYCHEM monitoring and control systems.

SPECIFICATIONS

Sensor housing & cap	Aluminum A380; Type 4X
Sensor sheath	316 stainless steel
Range	-100°F to 900°F (-73°C to 482°C) maximum
Accuracy	±1°F (0.5°C) at 32°F (0°C)
Resistance	100 ohms at 0°C α = 0.00385 ohms/ohm/°C
Connection	3/4-in (19 mm) NPT conduit hub Note: The length of RTD extension wires is determined by the wire gauge used. To reduce the likelihood that electrical noise will affect temperature measurement, keep RTD extension wires as short as possible. Use shielded instrument cable such as RAYCHEM MONI-RTD-WIRE (22 AWG, PVC insulation, -30°F to 140°F, -20°C to 60°C) or Belden 83553 (22 AWG, FEP insulation, -95°F to 395°F, -70°C to 200°C).
Operating Ambient	-40°F to 212°F (-40°C to 100°C) for all gas groups except Group A. -4°F to 212°F (-20°C to 100°C) for gas Group A

ADDITIONAL MATERIALS REQUIRED


Pipe strap, conduit, 16–22 AWG shielded instrument cable

KIT CONTENTS

One RTD temperature sensor

APPROVALS

The RTD7AL is CSA certified to U.S. and Canadian standards.



North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com



[nVent.com/RAYCHEM](https://www.nvent.com/RAYCHEM)

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER