



# 1-Phase 208V 20A switched PDU drawing & specification

RP1000: [Strip level measurement, SNMP Hardware](#)



### Single phase switched PDU

Input Rating : 20A, 208V  
 Outlet : 10A Rated C13 x 21  
 16A Rated C19 x 3  
 Inlet : 20A NEMA L6-20P plug  
 Cordset : 3 meter 12AWG cordset  
 Protection : NIL  
 Circuit Details : Output 16A max. C13 #1-21 + C19 #C1-C3

### Meter Features ( WS Switched PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Outlet Control : Outlet Switch ON / OFF  
 Accuracy : ±1% Billing-grade  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : V2 / V3 via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor


EMC Compliance : FCC Part 15 Subpart B certified  
 Safety Compliance : cTUVus Mark to UL 60950-1:2007/R:2014-10  
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
 UL 62368-1:2014  
 CAN/CSA-C22.2 No. 62368-1:2014  
 Environment Compliance : RoHS2 & REACH  
 UL 60730-1 Ed.5 (2016)

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Chassis Material : Steel  
 Chassis Color : Black  
 Product Dimension : 2.1 (W) x 3.1 (D) x 53.1 (H) inch  
 Net Weight : 12.7 lbs  
 Packing Dimension ( for 2 PDUs ) : 4.3 (W) x 10.6 (D) x 80.4 (H) inch  
 PDU Gross Weight ( for 2 PDUs ) : 33.8 lbs

### Mounting Method

VMS :



VMB :

Top feed

Bottom feed

