

Declaration of Conformity

Issued by Manufacturer
Hoffman Enclosures, Inc.
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.
declare at our sole responsibility, that these devices are designed and constructed according to
the fundamental safety and health requirements.

Enclosure Models: AST****R (Bulletin S90T)
Equipment Description: Hoffman Splitter Trough, Type 1
Enclosure Rating : CSA Type 1
Enclosure Certification: CSA C22.2 No. 76-14

PRODUCTS

CLASS 4662 02 - WIREWAYS AND BUSWAYS - Splitters

Splitter troughs in a general-purpose, sheet steel (Type 1) enclosure; Cat. Number Series ASTXXX3R and ASTXXX4R; containing terminal blocks suitable for copper only 3 or 4 wires, rated 85 to 225 Amp, 600 Vac max.

Splitter troughs in a general-purpose, sheet steel (Type 1) enclosure; Cat. Number Series ASTXXX3R and ASTXXX4R; containing terminal blocks suitable for copper only 3 or 4 wires, rated 400 to 600 Amp, 600 Vac max.

Applicable Standards: CAN/CSA C22.2 No. 76-14 – Splitters
CAN/CSA C22.2 No. 26-13 – Construction and Test of Wireways,
Auxiliary Gutters, and Associated Fittings

Authorized by:



5/22/2020 (today's date)

Glen Kampa

Date

Senior Regulatory Engineer

Subject to Change Without Notice

DOC: CERT-00270-B



Certificate of Compliance

Certificate: 70074096 **Master Contract:** 151630 (042184_C_000)
Project: 70177570 **Date Issued:** 2018-04-25
Issued to: Hoffman Enclosures Inc.
2100 Hoffman Way
Anoka, Minnesota 55303-1745
USA
Attention: Glen Kampa

The products listed below are eligible to bear the CSA Mark shown



Issued by: *Frank Gessner*
Frank Gessner

PRODUCTS

CLASS 4662 02 - WIREWAYS AND BUSWAYS - Splitters

Splitter troughs in a general-purpose, sheet steel (Type 1) enclosure; Cat. Number Series ASTXXX3R and ASTXXX4R; containing terminal blocks suitable for copper only 3 or 4 wires, rated 85 to 225 Amp, 600 Vac max.

Splitter troughs in a general-purpose, sheet steel (Type 1) enclosure; Cat. Number Series ASTXXX3R and ASTXXX4R; containing terminal blocks suitable for copper only 3 or 4 wires, rated 400 to 600 Amp, 600 Vac max.

APPLICABLE REQUIREMENTS

- CSA C22.2 No. 76-14 - Splitters
- CSA C22.2 No. 26-13 - Construction and Test of Wireways, Auxiliary Gutters, and Associated Fittings