


1-Phase 110V 30A switched PDU drawing & specification

RP2000: Strip level measurement, Outlet Switch ON / OFF, SNMP Hardware



Single phase switched PDU

Input Rating : 30A, 110V
 Outlet : 20A Rated US NEMA 5-20R x 24
 Inlet : 30A NEMA L5-30P plug
 Cordset : 3 meter UL 10AWG cordset
 Protection : 16A single pole hydraulic MCB x 2
 Circuit Details : < **Circuit A** > Output 12A max. U.S # 1 - 12
 < **Circuit B** > Output 12A max. U.S # 13 - 24

Meter Features (WS Switched PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : ±1% Billing-grade
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : V2 / V3 via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

Chassis Material : Steel
 Chassis Color : Black
 Product Dimension : 2.1 (W) x 3.1 (D) x 53.15 (H) mm
 Net Weight : 23.5 lbs
 Packing dimension (for 2 PDUs) : 4.3 (W) x 10.6 (D) x 70.6 (H) inch
 PDU gross weight (for 2 PDUs) : 55.4 lbs

EMC	Compliance	: FCC Part 15 Subpart B certified
Safety	Compliance	: cTUVus Mark to UL 60950-1:2007/R:2014-10 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10 UL 62368-1:2014 CAN/CSA-C22.2 No. 62368-1:2014 UL 60730-1 Ed.5 (2016)
Environment	Compliance	: RoHS2 & REACH
Operating Temperature		: -5 to 60 °C
Storage Temperature		: -25 to 65 °C
Operating Altitude		: 0 to 2,000 m
Storage Altitude		: 0 to 15,000 m
Humidity		: 8 to 95% RH, non-condensing