

Three phase switched PDU

Input Rating : 30A, 208V 3PH
 Outlet : 10A 208V Rated C13 x 21
 16A 208V Rated C19 x 3
 Inlet : 30 Amp NEMA L21-30P plug
 Cordset : 5-wire 2 meter STJ 10AWG cordset
 Protection : 20A 2-pole hydraulic MCB x 3
 Bank Details : < PH-1 > Output 17.3A max. C13 #1-7 + C19 #C1
 < PH-2 > Output 17.3A max. C13 #1-7 + C19 #C1
 < PH-3 > Output 17.3A max. C13 #1-7 + C19 #C1

Meter Features (WS Switched PDU)


Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : ±1% Billing-grade
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : V2 / V3 via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC Part 15 Subpart B certified
 Safety Compliance : cTUVus Mark to UL 60950-1:2007/R:2014-10
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10
 UL 62368-1:2014
 CAN/CSA-C22.2 No. 62368-1:2014
 Environment Compliance : UL 60730-1 Ed.5 (2016)
 : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Chassis Material : Steel
 Chassis Color : Black
 Product Dimension : 2.1 (W) x 3.1 (D) x 66.9 (H) inch
 Net weight : 17.6 lbs
 Packing Dimension (for 2 PDUs) : 4.3 (W) x 10.6 (D) x 80.4 (H) inch
 PDU gross weight (for 2 PDUs) : 39.6 lbs

Mounting Method



Top feed

Bottom feed

