




Front view



Top View



Rear view



unit : mm

Automatic transfer switch

Input Rating : 20A, 110V
 Outlet : 20A Rated US NEMA 5-20R x 16
 Inlet : 20A NEMA L5-20P plug x 2
 Cordset : 3 meter UL SJT 12 AWG cordset x 2
 Protection : 20A single pole hydraulic MCB x 1
 Circuit Details : Output 16A max. US #1 - 16

ATS Specification

Nominal input voltage : 110V
 Acceptable input voltage : $\pm 10\%$ nominal
 Input frequency : 50 / 60Hz
 Transfer time : 10 ms typical
 Electrical endurance : 1×10^5 operations
 Power consumption : Approx. 20W

Meter Features (WS - Outlet Switched)

Local Display : Field replaceable 2" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : $\pm 1\%$ Billing-grade
 SNMP : V2 / V3 via IP dongle

Chassis Material : Steel
 Chassis Color : Black
 Product Dimension : 17.2 (W) x 17.7 (D) x 3.5 (H) inch
 Packing Dimension : -
 Gross Weight : -
 Net Weight : -

EMC Compliance : FCC Part 15 Subpart B
 Safety Compliance : CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10
 UL 62368-1:2014
 CAN/CSA-C22.2 No. 62368-1:2014
 UL 60730-1 Ed.5 (2016)
 Environment Compliance : RoHS2 & REACH
 Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing