

Product name:CADWELD® Mold Sealer (T403)Page:1/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

Product identifier

Product name: CADWELD® Mold Sealer (T403)

Relevant identified uses of the substance or mixture and uses advised against

Application: Sealer.

Details of the supplier of the safety data sheet

Manufacturer: nVent

ERICO International Corporation

34600 Solon Road Solon, Ohio 44139 Tel:(440) 248-0100

Supplier: nVent

ERICO Products Australia 323 Parramatta Rd AUBURN NSW 2144

Further information can be

Jacob.Williams@nVent.com

obtained from:

Emergency telephone number

Emergency telephone: Australian Poisons Information Centre: 13 11 26.

SECTION 2: HAZARDS IDENTIFICATION

Classification of the substance or mixture

WHS: Not classified.

Label elements

The substance/mixture does not meet the criteria for classification of the Model Work Health and Safety Regulations and the SDS contains all the information

required by the WHS Regulations.

Additional information is listed in the safety data sheet.

Other hazards

Other: Dust may irritate throat and respiratory system and cause coughing. The product

may contain crystalline quartz in respirable fraction.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Mixtures

Only classified substances above threshold limits are shown.

Product name:CADWELD® Mold Sealer (T403)Page:2/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

WHS:

<u>%:</u>	CAS-No.:	EC No.:	REACH Reg. No:	<u>Chemical name:</u>	Hazard classification:	Notes:
10-20	1332-58-7	310-194-1	-	Kaolin	-	#
1-<4.5	1303-96-4		-	Disodium tetraborate Decahydrate	Repr. 1B;H360	SCL
0.1-<1	14808-60-7	238-878-4	-	Quartz (respirable dust)	-	#

Notes: #: The substance has been assigned an exposure limit.

SCL: Specific Concentration Limit

References: The full text for all hazard statements is displayed in section 16.

SECTION 4: FIRST AID MEASURES

Description of first aid measures

Inhalation: Dust inhalation: Move into fresh air and keep at rest. Get medical attention if any

discomfort continues.

Skin contact: Remove contaminated clothing immediately and wash skin with soap and water.

Then apply a fatty cream.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. Remove any

contact lenses and open eyelids widely. If irritation persists: Seek medical

attention and bring along these instructions.

Immediately rinse mouth and drink plenty of water. Keep person under

observation. If person becomes uncomfortable seek hospital and bring these

instructions.

Most important symptoms and effects, both acute and delayed

See section 11 for more detailed information on health effects and symptoms.

Indication of any immediate medical attention and special treatment needed

Medical attention/treatments: Treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

Extinguishing media

Extinguishing media: Use fire-extinguishing media appropriate for surrounding materials.

Special hazards arising from the substance or mixture

<u>Specific hazards:</u> No specific precautions.

Advice for firefighters

Protective equipment for fire- Selection of respiratory protection for fire fighting: follow the general fire

<u>fighters:</u> precautions indicated in the workplace.

Product name:CADWELD® Mold Sealer (T403)Page:3/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

<u>Personal precautions:</u> Avoid generation and spreading of dust. Avoid inhalation of dust.

Environmental precautions

Environmental No special precautions.

precautions:

Methods and material for containment and cleaning up

<u>Spill Cleanup Methods:</u> Collect spillage with shovel, broom or the like.

Reference to other sections

<u>References:</u> For personal protection, see section 8. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

Precautions for safe handling

Safe handling advice: Avoid inhalation of dust and contact with skin and eyes. Change contaminated

clothing.

<u>Technical measures:</u> Avoid spreading dust.

Conditions for safe storage, including any incompatibilities

<u>Technical measures for safe</u> No special precautions.

storage:

Storage conditions: Store in tightly closed original container in a dry and cool place. Protect from

moisture.

Specific end use(s)

Specific use(s): Sealer.

Product name:CADWELD® Mold Sealer (T403)Page:4/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Occupational exposure limits:

CAS-No.:	Chemical name:	As:	Exposure limits:	Type:	Notes:	References
1303-96-4	Borates, tetra, sodium salts (Decahydrate)	-	5 mg/m3	TWA	-	<u>:</u> WES
1332-58-7	Kaolin (inhalable dust)	-	10 mg/m3	TWA	-	WES
14808-60-7	Quartz (respirable dust)	-	0.05 mg/m3	TWA	Carc. 1A	WES
	14/50					

Notes: WES: Workplace exposure standards for airborne contaminants.

Exposure controls

Engineering measures: Provide adequate ventilation. Observe occupational exposure limits and

minimise the risk of inhalation of dust.

<u>Personal protection:</u> Personal protection equipment should be chosen according to relevant

AS/NZS standards and in discussion with the supplier of the personal protective equipment. Protective gloves and goggles are recommended.

Respiratory equipment: No specific recommendation made, but respiratory protection must be used if

the general level exceeds the recommended occupational exposure limit.

Hand protection: Risk of contact: Wear protective gloves. The most suitable glove must be

chosen in consultation with the gloves supplier, who can inform about the

breakthrough time of the glove material.

Eye protection: Safety glasses recommended.

Skin protection: No special precautions.

<u>Hygiene measures:</u> Wash hands after handling. Change contaminated clothing. Wash

contaminated clothing before reuse.

Product name:CADWELD® Mold Sealer (T403)Page:5/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance: Solid.

Form: Dough-like Odour: Dough-like Odour threshold: Not available. pH: Not available. Melting point / freezing point: Not available. **Boiling point:** Not available. Flash point: Not available. Evaporation rate: Not available.

Explosion limits: Not available.

Vapour pressure: Not available.

<u>Vapour density:</u> Not available.

<u>Relative density:</u> Not available.

Solubility: Slightly soluble in water.

Partition coefficient (n-

octanol/water):

Not available.

Auto-ignition Not available.

temperature (°C):

<u>Decomposition</u> Not available.

temperature (°C):

<u>Viscosity:</u> Not available. <u>Oxidising properties:</u> Not available.

Other information

Other data: Specific Gravity (Water=1): 2.0

Product name:CADWELD® Mold Sealer (T403)Page:6/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 10: STABILITY AND REACTIVITY

Reactivity

Reactivity: Not reactive.

Chemical stability

<u>Stability:</u> Stable under normal temperature conditions.

Possibility of hazardous reactions

<u>Hazardous Reactions:</u> None known.

Conditions to avoid

Conditions/materials to avoid: None known.

Incompatible materials

<u>Incompatible materials:</u> None known.

Hazardous decomposition products

<u>Hazardous decomposition</u> Polymerization will not occur.

products:

Product name: CADWELD® Mold Sealer (T403) 7/9 Page: 2016-05-04 Supersedes date: 2020-04-30 Revision: SDS-ID: CADWELD_MS_AU Version number: AU-EN/4.0

SECTION 11: TOXICOLOGICAL INFORMATION

Information on toxicological effects

Acute Toxicity (Oral): Based on available data, the classification criteria are not met. Acute Toxicity (Dermal): Based on available data, the classification criteria are not met. Acute Toxicity (Inhalation): Based on available data, the classification criteria are not met. Skin Corrosion/Irritation: Based on available data, the classification criteria are not met. Serious eye damage/irritation: Based on available data, the classification criteria are not met. Respiratory or skin Based on available data, the classification criteria are not met.

sensitisation:

Germ cell mutagenicity: Based on available data, the classification criteria are not met. Carcinogenicity: Based on available data, the classification criteria are not met. Based on available data, the classification criteria are not met. Reproductive Toxicity:

STOT - Single exposure: Based on available data, the classification criteria are not met. STOT - Repeated exposure: Based on available data, the classification criteria are not met. Aspiration hazard: Based on available data, the classification criteria are not met.

Inhalation: Dust may irritate throat and respiratory system and cause coughing.

Skin contact: Prolonged contact may cause redness, irritation and dry skin.

Eye contact: May irritate and cause redness and pain.

Ingestion: Ingestion may cause severe irritation of the mouth, the oesophagus and the

gastrointestinal tract.

Specific effects: Frequent inhalation of dust over a long period of time increases the risk of

developing lung diseases. Contains small amounts of a substance which is suspected to be harmful to the unborn child and to the reproduction capability.

(Borax)

IARC Cancer Review: Group 2B for Titanium dioxide.

IARC Carcinogen Group 1. (Quartz).

Product name:CADWELD® Mold Sealer (T403)Page:8/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 12: ECOLOGICAL INFORMATION

Toxicity

Ecotoxicity: The environmental hazard of the product is considered to be limited.

Persistence and degradability

<u>Degradability:</u> The product is not biodegradable.

Bioaccumulative potential

Bioaccumulative potential: No data available on bioaccumulation.

Mobility in soil

<u>Mobility:</u> The product is insoluble in water and will sediment in water systems.

Results of PBT and vPvB assessment

PBT/vPvB: This product does not contain any PBT or vPvB substances.

Other adverse effects

Other adverse effects: None known.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

Reacted/Used Product - can be disposed of as a non-hazardous waste.

Unreacted, spilled product - should be cleaned up and disposed of as hazardous waste.

SECTION 14: TRANSPORT INFORMATION

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADG).

UN number

UN-No:

UN proper shipping name

Proper Shipping Name: -

Transport hazard class(es)

<u>Class:</u> -

Packing group

PG: -

Environmental hazards

Marine pollutant: -

Environmentally Hazardous

substance:

Special precautions for user

<u>Special precautions:</u> Not relevant.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

<u>Transport in bulk:</u> Not relevant.

Product name:CADWELD® Mold Sealer (T403)Page:9/9Supersedes date:2016-05-04Revision:2020-04-30SDS-ID:CADWELD_MS_AUVersion number:AU-EN/4.0

SECTION 15: REGULATORY INFORMATION

Safety, health and environmental regulations/legislation specific for the substance or mixture

Special provisions: Disodium tetraborate DecahydrateAll chemicals included in the product are AICS

listed or exempted.

SUSMP: all ingredients are not listed or are excepted.

This product contains no ingredient above 0.1% listed in the WHS Regulations

2011, Schedule 10, Tables 10.1 and/or 10.2.

National regulation: Work Health and Safety Regulations 2011, with amendments.

National model Code of Practice for the Labelling of Workplace Hazardous

Chemicals (2018).

National model Code of Practice for the Preparation of Safety Data Sheets for

Hazardous Chemicals (2011), with amendments.

Workplace exposure standards for airborne contaminants (2019). Hazardous Waste (Regulation of Exports and Imports) Act 1989, with

amendments.

The Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP). The Industrial Chemicals (Notification and Assessment) Act 1989, as amended.

SECTION 16: OTHER INFORMATION

The user must be instructed in the proper work procedure and be familiar with the contents of these instructions.

The following sections contain revisions or new statements: 1, 2, 3, 8, 9, 11, 12, 14, 15, 16.

<u>Abbreviations and acronyms</u> PBT = Persistent, Bioaccumulative and Toxic. <u>used in the safety data sheet:</u> vPvB = very Persistent and very Bioaccumulative.

Additional information: Classification according to WHS Regulations 2011: Calculation method.

Wording of H-statements:

H360 May damage fertility or the unborn child.

The information on this data sheet represents our current data and is reliable provided that the product is used under the prescribed conditions and in accordance with the application specified on the packaging and/or in the technical guidance literature. Any other use of the product which involves using the product in combination with any other product or any other process is the responsibility of the user.