



Ref. Certif. No.

**DK-95207-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

### CB TEST CERTIFICATE

Product

LED luminaire for inside cabinet

Name and address of the applicant

PFEIFER & SEIBEL GMBH  
MAURERSTRASSE 15  
BREIDENBACH, 35236 Germany

Name and address of the manufacturer

PFEIFER & SEIBEL GMBH  
MAURERSTRASSE 15  
BREIDENBACH, 35236 Germany

Name and address of the factory

PFEIFER & SEIBEL GMBH  
MAURERSTRASSE 15  
BREIDENBACH, 35236 Germany

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

100-240 V~, 0.11-0.06 A, 50/60 Hz, 12 W, t<sub>a</sub> 55°C, Class II  
See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

EL1200MS See Page 2

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014/AMD1:2017, IEC 60598-1:2014, IEC 60598-2-1:1979/AMD1:1987, IEC 60598-2-1:1979

As shown in the Test Report Ref. No. which forms part of this Certificate

4788802535.3 issued on 2020-03-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-03-31

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-95207-UL**

Model Details:

Variants:

|              |             |
|--------------|-------------|
| EL1200DS     | EL900DS     |
| EL1200DS-GB  | EL900DS-GB  |
| EL1200DS-CH  | EL900DS-CH  |
| EL1200DS-BF  | EL900DS-BF  |
| EL1200DSR    | EL900DSR    |
| EL1200DSR-GB | EL900DSR-GB |
| EL1200DSR-CH | EL900DSR-CH |
| EL1200DSR-BF | EL900DSR-BF |
| EL1200MS     | EL900D      |
| EL1200MS-GB  | EL900DR     |
| EL1200MS-CH  |             |
| EL1200MS-BF  |             |
| EL1200MSR    |             |
| EL1200M      |             |
| EL1200MR     |             |

EL: Eldon

1200: 12W

900: 9W

D: with connector for external door switch

M: Motion sensor

S: with socket outlet

R: Supply connector rear (all models without R have supply connector on side)

GB: with british socket outlet, Type G

BF: with begium/france socket outlet Type E

CH: with switzerland socket outlet Type J

Additional Information:

Additionally evaluated to EN 60598-2-1:1989, EN 60598-1:2015/ A1:2018

National Differences specified in the CB Test Report

**Additional information (if necessary)**



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-03-31

Signature:

Jan-Erik Storgaard