


# ENEC LICENSE

**License No.** ENEC-02810-M1  
**Page** 1/3  
**Date of Issue** 2020-03-31

**License Holder** PFEIFER & SEIBEL GMBH  
MAURERSTRASSE 15  
BREIDENBACH, 35236 Germany  
**Production site** PFEIFER & SEIBEL GMBH  
MAURERSTRASSE 15  
BREIDENBACH, 35236 Germany  
**Certification Mark** See Annex 1  
**Certified Product** LED luminaire for inside cabinet  
**Model** EL1200MS See Page 2

**Trademark**



**Rated Voltage / Frequency** 100-240 V~, 0.11-0.06 A, 50/60 Hz  
**Rated Current / Power** 12 W See Page 2  
**Insulation Class** Class II  
**Degree of protection (IP)** IP 20  
**Tested acc. to** EN 60598-1:2015/A1:2018, EN 60598-1:2015, EN 60598-2-1:1989  
**Test Report No.** 4788802535.3 issued on 2020-03-20  
**Additional** ta 55°C

**Certification Manager**  
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

**Certification Body**

UL International Demko A/S, Borupvang 5A, DK-2750  
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com  
[www.ul-europe.com](http://www.ul-europe.com)



# ENEC LICENSE

License No. ENEC-02810-M1  
Page 2/3  
Date of Issue 2020-03-31

## Model Details:

### Variants:

EL1200DS	EL900DS
EL1200DS-GB	EL900DS-GB
EL1200DS-CH	EL900DS-CH
EL1200DS-BF	EL900DS-BF
EL1200DSR	EL900DSR
EL1200DSR-GB	EL900DSR-GB
EL1200DSR-CH	EL900DSR-CH
EL1200DSR-BF	EL900DSR-BF
EL1200MS	EL900D
EL1200MS-GB	EL900DR
EL1200MS-CH	
EL1200MS-BF	
EL1200MSR	
EL1200M	
EL1200MR	

EL: Eldon  
1200: 12W  
900: 9W

D: with connector for external door switch

M: Motion sensor

S: with socket outlet

R: Supply connector rear (all models without R have supply connector on side)

GB: with british socket outlet, Type G

BF: with begium/france socket outlet Type E

CH: with switzerland socket outlet Type J

The original report was modified to include the following changes/additions:

- Additional Trademark added
- New Marking plate with additional Trademark added
- Update of Critical Component List

The report was revised to include technical modifications

This certificate replaces the certificate No. ENEC-02810 issued on 2019-10-08.

### Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).



# Annex 1 to License No.

## ENEC-02810-M1

Annex of the form of the Mark



\* Identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio  $b/a=1,7$  is kept

\_\_\_\_\_  
**Certification Body**

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

