



* Endstücke geschraubt * Endcaps with screws * Embouts vissé

6 IEC – Kaltgerätedosen mit SI - Überstromschutz	6 IEC cold connector with overcurrent protection	6 prises IEC avec protection contre les surintensités
Steckdosen: <ul style="list-style-type: none">Nach IEC320 C132-polig mit Schutzkontakt;10A/2500W, AC250V, IP20,schwarz in Abdeckung RAL 7035	Sockets: <ul style="list-style-type: none">IEC 320 C132-pole with earthing contact;10A/2500W, AC250V, IP20,black in plastic part RAL 7035	Prises: <ul style="list-style-type: none">IEC 320 C132 pôles, 1 prise de terre10A/2500W, AC250V, IP20,noir in plastic RAL 7035
Anschluss: <ul style="list-style-type: none">wiederanschließbar;Kein Stromkabel; Stromeingang über Wieland GST18	Connection: <ul style="list-style-type: none">rewireable,no power cable; Power Input with Wieland GST18 connector	Connection: <ul style="list-style-type: none">Reconnection possiblePas de câble d'alimentationConnecteur Wieland GST18
Profil: 1HE, ALU, eloxiert;	Body: 1HE, ALU, anodized	Profilé: 1U, ALU, anodisé
Kunststoff: <ul style="list-style-type: none">RAL7035, PA6, Glasfaser 30%, Glühdrahtprüfung bis 850°C; V1	Plastic parts: <ul style="list-style-type: none">RAL7035, PA6, fibre glass 30%, Glow wire test up to 850° C ; V1	Éléments plastiques: <ul style="list-style-type: none">RAL7035, PA6, fibre de verre 30%, test au fil incandescent : jusqu'à 850° C ; V1
Haltewinkel: <ul style="list-style-type: none">Anschraubdrehmoment: ca. 2,0NMMontage in 90° - Schritten möglich;Für vertikale Montage, Artikelnr. 20110-068 separat bestellen.	Brackets: <ul style="list-style-type: none">Fastening force: aprox. 2,0 Nmmounting in 90° steps;For vertical fitting, item no. 20110-068, to order separately.	Equerres: <ul style="list-style-type: none">Couple de serrage: env. 2,0 NmMontage au pas de 90°;Montage vertical avec : réf. 20110-068, à commander séparément.
SI – Überstromschutz: <ul style="list-style-type: none">10A Nennstrom, 400V2-polig, Charakteristik B ; 6kA;	SI – overcurrent protection : <ul style="list-style-type: none">nominal current 10A, 400V2-poles, characteristic B ; 6kA ;	SI – protection <ul style="list-style-type: none">10A, 400V2-poles B; 6kA
Lieferform: <ul style="list-style-type: none">Neutrale Kartonverpackungmit Schroff Art.-Nr. und Barcode 39	Form of delivery: <ul style="list-style-type: none">Neutral carton boxWith Schroff Item no. and bar code 39	Conditionnement : <ul style="list-style-type: none">Emballage dans carton neutreAvec réf. Schroff et code barre 39
Lieferumfang: <ul style="list-style-type: none">1 x Steckdosenleiste2 x 19" Befestigungswinkel (Lose beigelegt)	Extent of delivery: <ul style="list-style-type: none">1 x Socket strip2 x 19" mounting brackets (Loose)	Composition : <ul style="list-style-type: none">1 x Bâti de prises2 x Equerre 19" (en vrac)
Thermische Eigenschaften <ul style="list-style-type: none">Betriebs- Umgebungstemperatur 0 ... +55°CLagertemperatur -20... +75°CBetriebs-Umgebungsfeuchte 5... 95% nicht kondensierend	Thermal specifications <ul style="list-style-type: none">Operating temperature range 0...+55°CStorage temperature range -20... +75°COperating humidity range 5...95% relative humidity, non-condensing	Spécification thermiques <ul style="list-style-type: none">Température de fonctionnement 0°.+55°Température de stockage -20°... +75°Humidité en fonctionnement 5%... 95% sans condensation