



nVent CADDY Low Voltage Accessory Clip



CONNECT AND PROTECT



When there is no other pathway for the growing amount of cable that must be accommodated in a building, our Low Voltage Accessory Clip (LVAC) is the answer. Part of the larger nVent CADDY datacom family of products, the LVAC will connect to the bottom or side of an existing pathway so you can accommodate more cable without rethinking the path. Quick, tool-free installation makes it easy to install in tight spaces.

Increase your cable routing and hanging options with the Low Voltage Accessory Clip.

FEATURES


- Ideal for low voltage applications, such as security, video, Wireless Access Protocol (WAP), Power over Ethernet (PoE), fire, control wire
- Tool-free installation to existing wire basket pathway made easy with side retaining flaps
- Designed to fit commonly available wire basket tray with bottom and side mount applications
- Modular ganging feature for ease of installation expansion
- Suitable for use in air handling (plenum) spaces
- Compliant with UL® 1565 and UL® 2043
- Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



Material: Polypropylene

Part Number	Cable Capacity 5e,6,6A	Diameter Ø	H	L	W	Color
LVACBA	22, 15, 8	1"	2 3/8"	2 3/8"	7/8"	Black
LVACRD	22, 15, 8	1"	2 3/8"	2 3/8"	7/8"	Red

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-E.9.7 and EN 50174-2. Cable capacity is calculated based on a 70% fill rate.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER