













Kabelverlegung an Betonbauteilen

CONNECT AND PROTECT



			MLT2HS6 (188100)	CT (170450) & MLT2HS6 (188100)	CTS1 (171600) & MLT2HS6 (188100)	QSC (182058)	QSC4 (182059)	PKM10H3 (182044)	PKM10H3GBSF (182053)	PKM10H6 (182045)	PKM10H6IN (182048)	PKM16H3 (182046)	PKM16H3GBSF (182054)	PKM16H6 (182047)	PKM16H6IN (182049)	nVent CADDY Cat HP J-Hook System		
Installationsart	Direktbefestigung mit Setzgerät																	
	Betonanker  	SCMDSN (800070)																
		SCMND (800071)																
		BSZSU06040ZL (402605)																
Anwendung	Deckenmontage (horizontal)		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	
	Wandmontage (vertikal)			✓	✓												✓	
	Edelstahlausführung Korrosionsschutz/Außenanwendung		✓		✓													
	Maximale Kabel Kapazität		1 >1	1 >1	1 >1	4	4	10	10	10	10	16	16	16	16	16	330	
	Funktionserhalt nach DIN 4102-12			✓	✓							✓				✓	✓	
	Geeignet für tragende Verkabelungssysteme gem BS7671-1:2018 in Kombination mit anderen Stahlbauteilen		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	

Legende:  Beste/empfohlene Installationsart **X** Alternativ moegliche Installationsart ✓ Geeignet