

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

CABLE MANAGEMENT- CABLE TRAY SYSTEMS

Name and address of the applicant

PEMSA CABLE MANAGEMENT, S.A.
PI LA GARENA, C/ GALILEO GALILEI, 22-24
28806 ALCALÁ DE HENARES (Madrid - Spain)

Name and address of the manufacturer

SAME AS ABOVE

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

REJIBAND

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61537:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

CEL-0331/15-1/1 to CEL-0331/15-1/6, CEL-1106/20-1_1 to CEL-1106/20-1_21

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
Cl Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2021-06-08


Signature: Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES1659-M1-AENOR

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Trade mark: REJIBAND

Product: CABLE MANAGEMENT- CABLE TRAY SYSTEMS

Type of accessory: REINFORCED JOINT CLAMP / PART CLAMP / CENTRAL HANGING M8-M10 / COVER

Reference	Width x Height (mm)	Safe working load (SWL)	Impact resistance	Surface treatment	Additional information
60211100	100x35	168 N/m	20 J	EZ3	64010061/64010060/67010046/73021100
60211150	150x35	90 N/m	20J	EZ3	64010061/64010060/67010046/73021150
60211200	200x35	215 N/m	20J	EZ3	64010061/64010060/67010046/73021200
60211300	300x35	164 N/m	20J	EZ3	64010061/64010060/67010046/73021300
60211400	400x35	227 N/m	20J	EZ3	64010061/64010060/67010046/73021400
60212060	60x60	274 N/m	20J	EZ3	64010061/64010060/67010046/73021060
60212100	100x60	405 N/m	20J	EZ3	64010061/64010060/67010046/73021100
60212150	150x60	299 N/m	20J	EZ3	64010061/64010060/67010046/73021150
60212200	200x60	320 N/m	20J	EZ3	64010061/64010060/67010046/73021200
60212300	300x60	538 N/m	20J	EZ3	64010061/64010060/67010046/73021300
60212400	400x60	553 N/m	20J	EZ3	64010061/64010060/67010046/73021400
60212450	450x60	460 N/m	20J	EZ3	64010061/64010060/67010046/73021450
60212500	500x60	667 N/m	20J	EZ3	64010061/64010060/67010046/73021500
60212600	600x60	646 N/m	20J	EZ3	64010061/64010060/67010046/73021600
60213100	100x100	523 N/m	20J	EZ3	64010061/64010060/67010046/73021100
60213150	150x100	458 N/m	20J	EZ3	64010061/64010060/67010046/73021150
60213200	200x100	654 N/m	20J	EZ3	64010061/64010060/67010046/73021200
60213300	300x100	863 N/m	20J	EZ3	64010061/64010060/67010046/73021300
60213400	400x100	733 N/m	20J	EZ3	64010061/64010060/67010046/73021400
60213450	450x100	618 N/m	20J	EZ3	64010061/64010060/67010046/73021450
60213500	500x100	858 N/m	20J	EZ3	64010061/64010060/67010046/73021500
60213600	600x100	973 N/m	20J	EZ3	64010061/64010060/67010046/73021600
60221100	100x35	168 N/m	20J	BYCRO	64020061/64020060/67020046/73021100
60221150	150x35	90 N/m	20J	BYCRO	64020061/64020060/67020046/73021150
60221200	200x35	215 N/m	20J	BYCRO	64020061/64020060/67020046/73021200
60221300	300x35	164 N/m	20J	BYCRO	64020061/64020060/67020046/73021300
60221400	400x35	227 N/m	20J	BYCRO	64020061/64020060/67020046/73021400
60222060	60x60	274 N/m	20J	BYCRO	64020061/64020060/67020046/73021060
60222100	100x60	405 N/m	20J	BYCRO	64020061/64020060/67020046/73021100
60222150	150x60	299 N/m	20J	BYCRO	64020061/64020060/67020046/73021150
60222200	200x60	320 N/m	20J	BYCRO	64020061/64020060/67020046/73021200
60222300	300x60	538 N/m	20J	BYCRO	64020061/64020060/67020046/73021300
60222400	400x60	553 N/m	20J	BYCRO	64020061/64020060/67020046/73021400
60222450	450x60	460 N/m	20J	BYCRO	64020061/64020060/67020046/73021450
60222500	500x60	667 N/m	20J	BYCRO	64020061/64020060/67020046/73021500
60222600	600x60	646 N/m	20J	BYCRO	64020061/64020060/67020046/73021600
60223100	100x100	523 N/m	20J	BYCRO	64020061/64020060/67020046/73021100
60223150	150x100	458 N/m	20J	BYCRO	64020061/64020060/67020046/73021150
60223200	200x100	654 N/m	20J	BYCRO	64020061/64020060/67020046/73021200
60223300	300x100	863 N/m	20J	BYCRO	64020061/64020060/67020046/73021300
60223400	400x100	733 N/m	20J	BYCRO	64020061/64020060/67020046/73021400
60223450	450x100	618 N/m	20J	BYCRO	64020061/64020060/67020046/73021450
60223500	500x100	858 N/m	20J	BYCRO	64020061/64020060/67020046/73021500
60223600	600x100	973 N/m	20J	BYCRO	64020061/64020060/67020046/73021600
60231100	100x35	168 N/m	20J	HDG	64030061/64030060/67030046/73031100
60231150	150x35	90 N/m	20J	HDG	64030061/64030060/67030046/73031150
60231200	200x35	215 N/m	20J	HDG	64030061/64030060/67030046/73031200
60231300	300x35	164 N/m	20J	HDG	64030061/64030060/67030046/73031300
60231400	400x35	227 N/m	20J	HDG	64030061/64030060/67030046/73031400
60232060	60x60	274 N/m	20J	HDG	64030061/64030060/67030046/73031060
60232100	100x60	405 N/m	20J	HDG	64030061/64030060/67030046/73031100
60232150	150x60	299 N/m	20J	HDG	64030061/64030060/67030046/73031150
60232200	200x60	320 N/m	20J	HDG	64030061/64030060/67030046/73031200
60232300	300x60	538 N/m	20J	HDG	64030061/64030060/67030046/73031300
60232400	400x60	553 N/m	20J	HDG	64030061/64030060/67030046/73031400
60232450	450x60	460 N/m	20J	HDG	64030061/64030060/67030046/73031450
60232500	500x60	667 N/m	20J	HDG	64030061/64030060/67030046/73031500
60232600	600x60	646 N/m	20J	HDG	64030061/64030060/67030046/73031600
60233100	100x100	523 N/m	20J	HDG	64030061/64030060/67030046/73031100

ANNEX TO CB CERTIFICATE N° ES1659-M1-AENOR

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Reference	Width x Height (mm)	Safe working load (SWL)	Impact resistance	Surface treatment	Additional information
60233150	150x100	458 N/m	20J	HDG	64030061/64030060/67030046/73031150
60233200	200x100	654 N/m	20J	HDG	64030061/64030060/67030046/73031200
60233300	300x100	863 N/m	20J	HDG	64030061/64030060/67030046/73031300
60233400	400x100	733 N/m	20J	HDG	64030061/64030060/67030046/73031400
60233450	450x100	618 N/m	20J	HDG	64030061/64030060/67030046/73031450
60233500	500x100	858 N/m	20J	HDG	64030061/64030060/67030046/73031500
60233600	600x100	973 N/m	20J	HDG	64030061/64030060/67030046/73031600
60251200	200x35	258 N/m	20J	I304	64060061/64060060/67060046/73051200
60251300	300x35	255 N/m	20J	I304	64060061/64060060/67060046/73051300
60251400	400x35	307 N/m	20J	I304	64060061/64060060/67060046/73051400
60252100	100x60	353 N/m	20J	I304	64060061/64060060/67060046/73051100
60252150	150x60	356 N/m	20J	I304	64060061/64060060/67060046/73051150
60252200	200x60	405 N/m	20J	I304	64060061/64060060/67060046/73051200
60252300	300x60	409 N/m	20J	I304	64060061/64060060/67060046/73051300
60252400	400x60	413 N/m	20J	I304	64060061/64060060/67060046/73051400
60252500	500x60	526 N/m	20J	I304	64060061/64060060/67060046/73051500
60252600	600x60	640 N/m	20J	I304	64060061/64060060/67060046/73051600
60253100	100x100	600 N/m	20J	I304	64060061/64060060/67060046/73051100
60253150	150x100	600 N/m	20J	I304	64060061/64060060/67060046/73051150
60253200	200x100	600 N/m	20J	I304	64060061/64060060/67060046/73051200
60253300	300x100	617 N/m	20J	I304	64060061/64060060/67060046/73051300
60253400	400x100	640 N/m	20J	I304	64060061/64060060/67060046/73051400
60253500	500x100	664 N/m	20J	I304	64060061/64060060/67060046/73051500
60253600	600x100	688 N/m	20J	I304	64060061/64060060/67060046/73061600
60261200	200x35	258 N/m	20J	I316L	64060061/64060060/67060046/73061200
60261300	300x35	255 N/m	20J	I316L	64060061/64060060/67060046/73061300
60261400	400x35	307 N/m	20J	I316L	64060061/64060060/67060046/73061400
60262100	100x60	353 N/m	20J	I316L	64060061/64060060/67060046/73061100
60262150	150x60	356 N/m	20J	I316L	64060061/64060060/67060046/73061150
60262200	200x60	405 N/m	20J	I316L	64060061/64060060/67060046/73061200
60262300	300x60	409 N/m	20J	I316L	64060061/64060060/67060046/73061300
60262400	400x60	413 N/m	20J	I316L	64060061/64060060/67060046/73061400
60262500	500x60	526 N/m	20J	I316L	64060061/64060060/67060046/73061500
60262600	600x60	640 N/m	20J	I316L	64060061/64060060/67060046/73061600
60263100	100x100	600 N/m	20J	I316L	64060061/64060060/67060046/73061100
60263150	150x100	600 N/m	20J	I316L	64060061/64060060/67060046/73061150
60263200	200x100	600 N/m	20J	I316L	64060061/64060060/67060046/73061200
60263300	300x100	617 N/m	20J	I316L	64060061/64060060/67060046/73061300
60263400	400x100	640 N/m	20J	I316L	64060061/64060060/67060046/73061400
60263500	500x100	664 N/m	20J	I316L	64060061/64060060/67060046/73061500
60263600	600x100	688 N/m	20J	I316L	64060061/64060060/67060046/73061600
60281100	100x35	168 N/m	20J	BLACK C8	64080061/64080060/67080046/82002532
60281150	150x35	90 N/m	20J	BLACK C8	64080061/64080060/67080046/82002533
60281200	200x35	215 N/m	20J	BLACK C8	64080061/64080060/67080046/82002534
60281300	300x35	164 N/m	20J	BLACK C8	64080061/64080060/67080046/82002535
60281400	400x35	227 N/m	20J	BLACK C8	64080061/64080060/67080046/82002536
60282060	60x60	274 N/m	20J	BLACK C8	64080061/64080060/67080046/82002531
60282100	100x60	405 N/m	20J	BLACK C8	64080061/64080060/67080046/82002532
60282150	150x60	299 N/m	20J	BLACK C8	64080061/64080060/67080046/82002533
60282200	200x60	320 N/m	20J	BLACK C8	64080061/64080060/67080046/82002534
60282300	300x60	538 N/m	20J	BLACK C8	64080061/64080060/67080046/82002535
60282400	400x60	553 N/m	20J	BLACK C8	64080061/64080060/67080046/82002536
60282450	450x60	460 N/m	20J	BLACK C8	64080061/64080060/67080046
60282500	500x60	667 N/m	20J	BLACK C8	64080061/64080060/67080046/82002537
60282600	600x60	646 N/m	20J	BLACK C8	64080061/64080060/67080046/82002538
60283100	100x100	523 N/m	20J	BLACK C8	64080061/64080060/67080046/82002532
60283150	150x100	458 N/m	20J	BLACK C8	64080061/64080060/67080046/82002533
60283200	200x100	654 N/m	20J	BLACK C8	64080061/64080060/67080046/82002534
60283300	300x100	863 N/m	20J	BLACK C8	64080061/64080060/67080046/82002535
60283400	400x100	733 N/m	20J	BLACK C8	64080061/64080060/67080046/82002536
60283450	450x100	618 N/m	20J	BLACK C8	64080061/64080060/67080046
60283500	500x100	858 N/m	20J	BLACK C8	64080061/64080060/67080046/82002537
60283600	600x100	973 N/m	20J	BLACK C8	64080061/64080060/67080046/82002538

ANNEX TO CB CERTIFICATE N° ES1659-M1-AENOR

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Classification:

6.1 According to material: **Metallic**

6.2 According to resistance to flame: **No flame propagation**

6.3 Electrical continuity: **With Electrical continuity**

- Maximum impedance of a joint of cable trays: **< 50 mOhm**

- Maximum impedance along the length of a cable tray: **< 5 mOhm /m**

6.4 Electrical conductivity: **Conductive**

6.5 Resistance against corrosion:

- Electrogalvanised (System EZ, Finish EZ3) - **Class C3**

- Electrogalvanised Bichromate (System BC, Finish BYCRO) - **Class C5**

- Hot Dip Galvanised (System GC, Finish HDG) - **Class C7**

- Electrogalvanised High Resistance (System BK8, Finish BLACK C8) - **Class C8**

- Stainless Steel AISI 304 (System INOX, Finish I304) - **Class C9C**

- Stainless Steel AISI 316L (System INOX, Finish I316L) - **Class C9D**

6.6 According to temperature:

- Minimum temperatura for transport, storage, installation and use: **- 50 °C**

- Maximum temperatura for transport, storage, installation and use: **150 °C**

6.7 According to perforation in the base área: **D Classification**

6.9 According to impact resistance: **Up to 20 J**

10.2 SWL test (Safety Working Load):

- Cable tray (span tested): **1,5 m**