

Declaration of Conformity

Issued by Manufacturer Hoffman Enclosures, Inc.
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.

declare at our sole responsibility, that these devices are designed and constructed according to the fundamental safety and health requirements.

Enclosure Models: ADLTEMP, AMHUM, ATEMNC, ATEMNO (bulletin D85)

Equipment Description: Hoffman Thermostats and Hygrostat

Equipment Certification: cURus Recognized E164102 ; CSA 215952

Applicable Standards: UL 873 Temperature Indicating and Regulating Equipment
UL 60730 Automatic Electrical Controls for Household and Similar Use
CSA E60730 Automated Electrical Controls
CSA C22.2 No.24 Temperature Indicating and Regulating Equipment

Authorized by:



2/18/2022

Tom Hurney

Date

Technology Mgr., Product Compliance and Approvals



Temperature-indicating and -Regulating Equipment - Component

[See General Information for Temperature-indicating and -Regulating Equipment - Component](#)

STEGO ELEKTROTECHNIK GMBH

E164102

Kolpingstrasse 21

74523 Schwaebisch Hall, GERMANY

Electronic Humidity regulating controls Model(s) EFL012462 followed by two numeric digits

EFR01246 followed by 0 or 9, followed by two numeric digits

Electronic temperature regulating controls Model(s) ETL011312 followed by two numeric digits

ETR01132 followed by 0 or 9, followed by two numeric digits

Regulating thermostats Model(s) STS 011 followed by five alphanumeric digits

Investigated to UL-60730-1

Electronic Humidity regulating controls Model(s) EFL012452 followed by two numeric digits

EFR01245 followed by 0 or 9, followed by two numeric digits

Electronic temperature regulating controls Model(s) ETL011322 followed by two numeric digits

ETR01131 followed by 0 or 9, followed by two numeric digits

Humidity and temperature regulating control Model(s) ETF 0123 followed by 0 or 1, followed by 0, 1 or 9, followed by two numeric digits

Regulating thermostats Model(s) STO 011 followed by five alphanumeric digits

Investigated to UL-60730-1, UL 60730-2-9, UL 60730-2-13

Temperature-Indicating and -Regulating Equipment Model(s) DCT 010 and DCF 010

Humidity and temperature regulating control, "ETF" Model(s) Model ETF 0123, followed by 0 or 1, followed by 0, 1 or 9, followed by two numeric digits

Investigated to UL-60730-1, UL 60730-2-9

Electronic Temperature regulating controls, "ETL 011" Model(s) ETL, followed by 011, followed by 31 or 32, followed by 2, followed by two numeric digits

Electronic Temperature regulating controls, "ETR 011" Model(s) ETR, followed by 011, followed by 31 or 32, followed by 0 or 9, followed by two numeric digits

Regulating thermostats, "Series STO 011 and STS 011" Model(s) Models STO 011 and STS 011 followed by five alphanumeric digits

Investigated to UL 873

Regulating thermostats, "KTO 011 and KTS 011" Model(s) 01140.9-XX, 01141.9-XX, 01142.0-XX, 01142.9-XX, 01143.0-XX, 01143.9-XX, 01144.9-XX, 01145.9-XX, 01146.9-XX, 01147.9-XX, 01149.9-XX, 01156.0-XX, 01157.0-XX, 01158.0-XX, 01159.0-XX

Regulating thermostats, "ZR011" Model(s) 01172.0-00, 01172.0-01, 01175.0-00, 01175.0-01, 01176.0-00, 01176.0-01

Regulating thermostats, "ZR111" Model(s) 11172.0-00, 11177.0-00, 11178.0-00, 11179.0-00

Temperature regulating themostats, "FZK" Model(s) FZK 01170.9-01

Temperature regulating thermostats, "FZK" Model(s) FZK 01170.0-00, FZK 01170.0-01, FZK 01170.9-00

Temperature regulating therrmostats, "FZK" Model(s) FZK 01170.0-02

Investigated to UL-60730-1, UL 60730-2-13

Electronic Humidity regulating controls, "EFL 012" Model(s) EFL, followed by 012, followed by 45 or 46, followed by 2, followed by two numeric digits

Electronic Humidity regulating controls, "EFR 012" Model(s) EFR, followed by 012, followed by 45 or 46, followed by 0 or 9, followed by two numeric digits

Investigated to UL-60730-1, UL 60730-2-9

Reggulating Thermostats Model(s) FTS 01161.0-06

Regulating Thermostats Model(s) FTD 01163.0-05

Regulating thermostats Model(s) FTD 01163.0-09, FTD 01163.0-10

Regulating Thermostats Model(s) FTD 01164.0-01, FTD 01166.0-00, FTO 01160.0-03

Regulating thermostats Model(s) FTO 01160.0-05

Regulating Thermostats Model(s) FTO 01160.0-09, FTS 01161.0-04, FTS 01161.0-08, FTS 01161.0-09, FTS 01161.0-10

Regulationg Thermostats Model(s) FTO 01160.0-10

Regulating thermostats, "FTD" Model(s) FTD 011630-00, FTD 011630-01, FTD 011630-02, FTD 011630-03, FTD 011630-08, FTD 011640-00, FTD 011640-01, FTD 011640-02, FTD 011640-03, FTD 011640-08, FTD 011650-01, FTD 011650-02, FTD 011650-03, FTD 011650-08


Regulating thermostats, "FTO" Model(s) FTO 011600-00, FTO 011600-01

Regulating thermostats, "FTS" Model(s) FTS 011610-00, FTS 011610-01, FTS 011610-02, FTS 011610-03, FTS 011620-00, FTS 011620-01, FTS 011620-02, FTS 011620-03

Investigated to UL-60730-1

Humidity and temperature controls, "MFR" Model(s) MFR 01220.0-00

XX - Where XX can be 00 - 99.

Marking: Company name or tradename "E164102" or trademark  and model designation.

[Last Updated](#) on 2019-10-14

Schwaebisch Hall, 74523 Germany

CCN Changes

If you notice a change to your Listing Card.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2020 UL LLC"

Temperature-indicating and -Regulating Equipment Certified for Canada - Component

[See General Information for Temperature-indicating and -Regulating Equipment Certified for Canada - Component](#)

STEGO ELEKTROTECHNIK GMBH

E164102

Kolpingstrasse 21

74523 Schwaebisch Hall, GERMANY

Electronic Humidity regulating controls Model(s) EFL012462 followed by two numeric digits

EFR01246 followed by 0 or 9, followed by two numeric digits

Electronic temperature regulating controls Model(s) ETL011312 followed by two numeric digits

ETR01132 followed by 0 or 9, followed by two numeric digits

Regulating thermostats Model(s) STS 011 followed by five alphanumeric digits

Investigated to CAN/CSA-E60730-1

Electronic Humidity regulating controls Model(s) EFL012452 followed by two numeric digits

EFR01245 followed by 0 or 9, followed by two numeric digits

Electronic temperature regulating controls Model(s) ETL011322 followed by two numeric digits

ETR01131 followed by 0 or 9, followed by two numeric digits

Humidity and temperature regulating control Model(s) ETF 0123 followed by 0 or 1, followed by 0, 1 or 9, followed by two numeric digits

Regulating thermostats Model(s) STO 011 followed by five alphanumeric digits

Investigated to CSA-C22.2 No. 24-93, CAN/CSA-E60730-1, CAN/CSA-E730-2-9, CAN/CSA-E730-2-13

Temperature-Indicating and -Regulating Equipment Model(s) DCT 010 and DCF 010

Investigated to CAN/CSA-E60730-1, CAN/CSA-E730-2-9

Regulating Thermostats Model(s) FTS 01161.0-06

Regulating Thermostats Model(s) FTD 01163.0-05

Regulating thermostats Model(s) FTD 01163.0-09, FTD 01163.0-10

Regulating Thermostats Model(s) FTD 01164.0-01, FTD 01166.0-00, FTO 01160.0-03

Regulating thermostats Model(s) FTO 01160.0-05

Regulating Thermostats Model(s) FTO 01160.0-09, FTS 01161.0-04, FTS 01161.0-08, FTS 01161.0-09, FTS 01161.0-10

Regulating Thermostats Model(s) FTO 01160.0-10

Investigated to CAN/CSA-E60730-1, CAN/CSA-E730-2-9, CAN/CSA-E730-2-13

Humidity and temperature regulating control, "ETF" Model(s) Model ETF 0123, followed by 0 or 1, followed by 0, 1 or 9, followed by two numeric digits

Investigated to CSA-C22.2 No. 24-93

Regulating thermostats, "KTO 011 and KTS 011" Model(s) 01140.9-XX, 01141.9-XX, 01142.0-XX, 01142.9-XX, 01143.0-XX, 01143.9-XX, 01144.9-XX, 01145.9-XX, 01146.9-XX, 01147.9-XX, 01149.9-XX, 01156.0-XX, 01157.0-XX, 01158.0-XX, 01159.0-XX

Regulating thermostats, "ZR011" Model(s) 01172.0-00, 01172.0-01, 01175.0-00, 01175.0-01, 01176.0-00, 01176.0-01

Regulating thermostats, "ZR111" Model(s) 11172.0-00, 11177.0-00, 11178.0-00, 11179.0-00

Temperature regulating thermostats, "FZK" Model(s) FZK 01170.9-01

Temperature regulating thermostats, "FZK" Model(s) FZK 01170.0-00, FZK 01170.0-01, FZK 01170.9-00

Temperature regulating thermostats, "FZK" Model(s) FZK 01170.0-02

Investigated to CAN/CSA-E60730-1, CAN/CSA-E730-2-9

Electronic Temperature regulating controls, "ETL 011" Model(s) ETL, followed by 011, followed by 31 or 32, followed by 2, followed by two numeric digits

Electronic Temperature regulating controls, "ETR 011" Model(s) ETR, followed by 011, followed by 31 or 32, followed by 0 or 9, followed by two numeric digits

Regulating thermostats, "FTD" Model(s) FTD 011630-00, FTD 011630-01, FTD 011630-02, FTD 011630-03, FTD 011630-08, FTD 011640-00, FTD 011640-01, FTD 011640-02, FTD 011640-03, FTD 011640-08, FTD 011650-01, FTD 011650-02, FTD 011650-03, FTD 011650-08

Regulating thermostats, "FTO" Model(s) FTO 011600-00, FTO 011600-01

Regulating thermostats, "FTS" Model(s) FTS 011610-00, FTS 011610-01, FTS 011610-02, FTS 011610-03, FTS 011620-00, FTS 011620-01, FTS 011620-02, FTS 011620-03

Regulating thermostats, "Series STO 011 and STS 011" Model(s) Models STO 011 and STS 011 followed by five alphanumeric digits

Investigated to CAN/CSA-E60730-1, CAN/CSA-E730-2-13



Electronic Humidity regulating controls, "EFL 012" Model(s) EFL, followed by 012, followed by 45 or 46, followed by 2, followed by two numeric digits

Electronic Humidity regulating controls, "EFR 012" Model(s) EFR, followed by 012, followed by 45 or 46, followed by 0 or 9, followed by two numeric digits

Investigated to CAN/CSA-E60730-1

Humidity and temperature controls, "MFR" Model(s) MFR 01220.0-00

XX - Where XX can be 00 - 99.

Marking: Company name or tradename "E164102" or trademark  , model designation and the Recognized Component Mark for Canada, 

Last Updated on 2019-10-14

STEGO ELEKTROTECHNIK GMBH
Kolpingstrasse 21
Schwaebisch Hall, 74523 Germany
CCN Changes

If you notice a change to your Listing Card.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2020 UL LLC"