

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	1/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## **SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**

### **1.1. Product identifier**

Product name: nVent® ERICO® Cadweld® One Shot  
Inclusive of material types: F20, F80, F33, XF19, F76  
Applicable prefixes: ACB, ACC, SCC, SB, PB, CA, XF

### **1.2. Relevant identified uses of the substance or mixture and uses advised against**

Application: Exothermic Welding material

### **1.3. Details of the supplier of the safety data sheet**

Manufacturer: nVent  
ERICO International Corporation  
34600 Solon Road  
Solon, Ohio 44139  
Tel:(440) 248-0100

Supplier: nVent  
ERICO Europe B.V.  
Jules Verneweg 75  
NL-5015 BG Tilburg  
Tel:+31 135835100

Further information can be obtained from: erico.compliance@nvent.com

### **1.4. Emergency telephone number**

Emergency telephone: NHS: 111  
  
Chemtel  
+01-813-248-0585 International

# SAFETY DATA SHEET

Product name: nVent® ERICO® Cadweld® One Shot  
Supersedes date:  
SDS-ID: CADWELD\_PLUS\_UK

Page: 2/12  
Revision: 2020-01-13  
Version number: GB-EN/1.0

## SECTION 2: HAZARDS IDENTIFICATION

### 2.1. Classification of the substance or mixture

CLP:  
Flam. Sol. 1;H228  
Acute Tox. 4;H302  
Acute Tox. 4;H332  
Eye Dam. 1;H318  
Aquatic Acute 1;H400  
Aquatic Chronic 1;H410

### 2.2. Label elements



DANGER

Contains: Dicopper oxide

H228 Flammable solid.

H302 Harmful if swallowed.

H332 Harmful if inhaled.

H318 Causes serious eye damage.

H410 Very toxic to aquatic life with long lasting effects.

P260 Do not breathe dust/fume

P280 Wear eye protection and gloves.

P301 + P312 IF SWALLOWED: Call a POISON CENTER/doctor/... if you feel unwell.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER/doctor.

P273 Avoid release to the environment.

### 2.3. Other hazards

PBT/vPvB: This product does not contain any PBT or vPvB substances.

Other: Improper use of the product or inadequate preparation of the conductors, moulds or surroundings can result in aggressive reactions. Dust may form explosive mixture with air. Self-propagating high temperature reaction will occur if heated above ignition temperature. Generates molten metal in excess of 1370°C, slag and dense, dusty smoke. The molten product can cause serious burns. Inhalation of powder or fumes may cause metal fume fever. Exposure to reaction by-products: See section 8.

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

Only classified substances above threshold limits or substances with an exposure limit are shown.

# SAFETY DATA SHEET

Product name: nVent® ERICO® Cadweld® One Shot

Page: 3/12

Supersedes date:

Revision: 2020-01-13

SDS-ID: CADWELD\_PLUS\_UK

Version number: GB-EN/1.0

## CLP:

<u>%:</u>	<u>CAS-No.:</u>	<u>EC No.:</u>	<u>REACH Reg. No.:</u>	<u>Chemical name:</u>	<u>Hazard classification:</u>	<u>Notes:</u>
25-85	1317-39-1	215-270-7	-	Dicopper oxide	Acute Tox. 4;H302 Acute Tox. 4;H332 Eye Dam. 1;H318 Aquatic Acute 1;H400 Aquatic Chronic 1;H410	
20-40	7429-90-5	231-072-3	-	Aluminium powder (stabilised)	Flam. Sol. 1;H228 Water-react. 2;H261 Skin Irrit. 2;H315 Eye Irrit. 2;H319 STOT SE 3;H335	
1-20	1317-38-0	215-269-1	-	Copper oxide	Aquatic Acute 1;H400 Aquatic Chronic 1;H410	
1-20	7440-50-8	231-159-6	-	Copper	Aquatic Acute 1;H400 Aquatic Chronic 3;H412	
1-5	7440-31-5	231-141-8	-	Tin	-	#
0.1-1	7789-75-5	232-188-7	-	Calcium fluoride	-	#

## References:

The full text for all hazard statements is displayed in section 16.

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	4/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 4: FIRST AID MEASURES

### **4.1. Description of first aid measures**

Molten product will cause skin burns and if in contact with eyes while in a molten state may cause serious damage.

Inhalation: Inhalation of welding fumes/Dust inhalation: Move into fresh air and keep at rest. In case of persistent throat irritation or coughing: Seek medical attention and bring these instructions.

Skin contact: Remove contaminated clothes and rinse skin thoroughly with water. If material is hot, treat for thermal burns and get immediate medical attention.

Eye contact: Dust in the eyes: Do not rub eye. Immediately flush with plenty of water for at least 15 minutes. Remove any contact lenses and open eyelids widely. If irritation persists: Seek medical attention and bring along these instructions.

Ingestion: Immediately rinse mouth and drink plenty of water. Keep person under observation. If person becomes uncomfortable seek hospital and bring these instructions.

### **4.2. Most important symptoms and effects, both acute and delayed**

Symptoms/effects: Inhalation of powder or fumes may cause metal fume fever. Symptoms like headache, fatigue and nausea may appear. See section 11 for more detailed information on health effects and symptoms.

### **4.3. Indication of any immediate medical attention and special treatment needed**

Medical attention/treatments: Burns (in contact with molten metal, slag or hot equipment): Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital.

## SECTION 5: FIREFIGHTING MEASURES

### **5.1. Extinguishing media**

Extinguishing media: Extinguish with dry sand and/or flood with large amounts of water.

Extinguishing media which are not suitable: Hand water buckets or hand storage pumps. Molten metal contact with water can cause small pockets of superheated steam.

Use fire-extinguishing media appropriate for surrounding materials.

### **5.2. Special hazards arising from the substance or mixture**

Specific hazards: During fire, gases hazardous to health may be formed.  
Ignition temperature: > 454 °C

Ignition of large quantities of exothermic materials may result in large volumes of dense smoke.

### **5.3. Advice for firefighters**

Protective equipment for fire-fighters: Selection of respiratory protection for fire fighting: follow the general fire precautions indicated in the workplace.

---

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	5/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### **6.1. Personal precautions, protective equipment and emergency procedures**

Personal precautions: Avoid inhalation of dust. Do not breathe fumes. Avoid contact with skin and eyes. Follow precautions for safe handling described in this safety data sheet.

Remove sources of ignition. Ventilate well.

### **6.2. Environmental precautions**

Environmental precautions: Precaution should be taken to prevent hot material and reaction byproducts from contact with combustible materials in surrounding areas. Avoid spreading dust or contaminated materials. Avoid discharge to the aquatic environment. Contact local authorities in case of spillage to drain/aquatic environment.

### **6.3. Methods and material for containment and cleaning up**

Methods for cleaning up: Remove sources of ignition. Sweep up spilled substance and remove to safe place.  
For large spills use natural fiber brush or broom with a conductive, non-sparking pan.

### **6.4. Reference to other sections**

References: For personal protection, see section 8. For waste disposal, see section 13.

## SECTION 7: HANDLING AND STORAGE

### **7.1. Precautions for safe handling**

Safe handling advice: Avoid inhalation of dust. Do not breathe fumes. Avoid contact with skin and eyes. Observe good chemical hygiene practices. nVent ERICO Cadweld Starting, Welding and Filler Materials are designed for use in nVent ERICO Cadweld equipment only. Use of improper or damaged equipment can lead to exposure to molten metal and reaction byproducts resulting in personal injury.

Technical measures: Do not smoke or use open fire or other sources of ignition. Work practice should minimise risk of contact.

Technical precautions: Confined space: Local exhaust is recommended.

### **7.2. Conditions for safe storage, including any incompatibilities**

Technical measures for safe storage: nVent ERICO Cadweld Starting, Welding and filler Materials should be stored in a clean, dry and secure location. Storage should include provisions to minimize rough handling, excessive vibration and physical abuse. All outer packages must be stored in accordance with label markings.

Storage conditions: If evidence is present of damaged or contaminated products, these units should not be used.

If proper storage is maintained, nVent ERICO Cadweld Materials do not exhibit any storage or shelf life.

### **7.3. Specific end use(s)**

Specific use(s): Welding material

---

# SAFETY DATA SHEET

Product name: nVent® ERICO® Cadweld® One Shot Page: 6/12  
Supersedes date: Revision: 2020-01-13  
SDS-ID: CADWELD\_PLUS\_UK Version number: GB-EN/1.0

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1. Control parameters

A detailed fume analysis was conducted on nVent ERICO Cadweld Starting and Welding Material. Reactions byproducts were tested for total dust, respirable dust, metals, acids, fluorides, and various elements identified in typical welding fume analysis. All sampling and analysis followed methodologies dictated by the National Institute of Occupational Safety and Health (NIOSH) and by the U.S. Occupational Safety and Health Administration (OSHA). A certified Industrial Hygienist did the sample collection.

Occupational exposure limits:

<u>CAS-No.:</u>	<u>Chemical name:</u>	<u>As:</u>	<u>Exposure limits:</u>	<u>Type:</u>	<u>Notes:</u>	<u>References</u>
7429-90-5	Aluminium metal, respirable dust	-	4 mg/m3	TWA	-	EH40
7429-90-5	Aluminium metal, inhalable dust	-	10 mg/m3	TWA	-	EH40
7440-21-3	Silicon, respirable dust	-	4 mg/m3	TWA	-	EH40
7440-21-3	Silicon, inhalable dust	-	10 mg/m3	TWA	-	EH40
7440-50-8	Copper, dusts and mists	Cu	1 mg/m3	TWA	-	EH40
		-	2 mg/m3	STEL	15min	
7440-50-8	Copper, fume	-	0.2 mg/m3	TWA	-	EH40
-	Tin compounds, inorganic (except SnH4)	Sn	2 mg/m3	TWA	-	EH40
		-	4 mg/m3	STEL	15min	
-	Fluoride (inorganic)	F	2.5 mg/m3	TWA	-	EH40

Notes: EH40: EH40/2005.

### 8.2. Exposure controls

Engineering measures: Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of dust and fumes.

Personal protection: Personal protection equipment should be chosen according to the relevant standards and in discussion with the supplier of the personal protective equipment. Use special welding equipment for protection of eyes, skin and respiratory system.

Respiratory equipment: Normal use precludes use of special protection as material is generally used out of doors, in small quantities and is of short duration. In case of inadequate ventilation and work of long duration or on large surface areas in confined rooms. Wear suitable respiratory equipment for dusts and metal fumes.

Hand protection: Heat insulated protective gloves. Recommended for handling hot equipment.

Eye protection: Wear goggles/face shield. Avoid direct eye contact with "flash" of light from reaction.

Skin protection: Use protective clothing, which covers arms and legs.

Hygiene measures: Wash hands after handling. Change contaminated clothing.

# SAFETY DATA SHEET

Product name: nVent® ERICO® Cadweld® One Shot  
Supersedes date:  
SDS-ID: CADWELD\_PLUS\_UK

Page: 7/12  
Revision: 2020-01-13  
Version number: GB-EN/1.0

---

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Form: Granular.  
Colour: Grey-black  
Odour: Odourless.  
pH: Not available.  
Melting point / freezing point: 600 °C  
Boiling point: Not available.  
Flash point: Not relevant.  
Evaporation rate: Not relevant.  
Vapour pressure: Not relevant.  
Vapour density: Not relevant.  
Solubility: Insoluble in water  
Partition coefficient (n-octanol/water): Not available.  
Auto-ignition temperature (°C): > 454 °C  
Decomposition temperature (°C): Not available.  
Viscosity: Not relevant.  
Explosive properties: Not available.  
Oxidising properties: Not available.

### 9.2. Other information

Other data: SPECIFIC GRAVITY (water=1) 4 - 5,5

---

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	8/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 10: STABILITY AND REACTIVITY

### **10.1. Reactivity**

Reactivity: See hazardous reactions.

### **10.2. Chemical stability**

Stability: Stable. Not sensitive to vibrations, shock or impact and is not subject to spontaneous ignition.

### **10.3. Possibility of hazardous reactions**

Hazardous Reactions: Aggressive reactions are possible if excess moisture is present in the mould or on the conductors to be welded. Care should be taken to ensure proper preparation in accordance with instruction prints.

### **10.4. Conditions to avoid**

Conditions/materials to avoid: Temperatures above ignition point. (454 °C)

### **10.5. Incompatible materials**

Incompatible materials: Typical of problems associated with molten metals.

### **10.6. Hazardous decomposition products**

Hazardous decomposition products: None under normal conditions. Polymerization will not occur.

---



# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	9/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 11: TOXICOLOGICAL INFORMATION

### 11.1. Information on toxicological effects

Acute Toxicity (Oral): Harmful if swallowed.

Acute Toxicity (Dermal): Based on available data, the classification criteria are not met.

Acute Toxicity (Inhalation): Harmful if inhaled.

Skin Corrosion/Irritation: Based on available data, the classification criteria are not met.

Serious eye damage/irritation: Causes serious eye damage.

Respiratory or skin sensitisation: Based on available data, the classification criteria are not met.

Germ cell mutagenicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Based on available data, the classification criteria are not met.

Reproductive Toxicity: Based on available data, the classification criteria are not met.

STOT - Single exposure: Based on available data, the classification criteria are not met.

STOT - Repeated exposure: Based on available data, the classification criteria are not met.

Aspiration hazard: Based on available data, the classification criteria are not met.

Inhalation: Dust may irritate throat and respiratory system and cause coughing. Heating above the melting point releases metallic oxides which may cause metal fume fever by inhalation. The symptoms are shivering, fever, malaise and muscular pain.

Skin contact: Dust has an irritating effect on moist skin. Prolonged and/or repeated contact: May cause eczema-like skin disorders (dermatitis). The molten product can cause serious burns.

Eye contact: Particles/fumes in the eyes may cause discomfort/irritation.

Ingestion: Ingestion may cause nausea, headache, dizziness and intoxication.

Specific effects: Frequent inhalation of dust over a long period of time increases the risk of developing lung diseases. Copper oxide may by repeated or prolonged inhalation occasionally cause ulceration and perforation of the nasal septum. Long term exposure to copper containing dusts may cause allergic dermatitis.

Toxicological data: LD50 (oral, rat): 1340 mg/kg (Dicopper oxide)

---

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	10/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 12: ECOLOGICAL INFORMATION

### 12.1. Toxicity

Ecotoxicity: Very toxic to aquatic life with long lasting effects.

Dicopper oxide:  
M-factor (acute): 100  
M-factor (chronic): 100

Copper oxide:  
M-factor (acute): 100  
M-factor (chronic): 100

Copper:  
M-factor (acute): 1

### 12.2. Persistence and degradability

Degradability: The product solely consists of inorganic compounds which are not biodegradable.

### 12.3. Bioaccumulative potential

Bioaccumulative potential: No data available on bioaccumulation.

### 12.4. Mobility in soil

Mobility: The product is not volatile but may be spread by dust-raising handling.

### 12.5. Results of PBT and vPvB assessment

PBT/vPvB: This product does not contain any PBT or vPvB substances.

### 12.6. Other adverse effects

Other adverse effects: None known.

## SECTION 13: DISPOSAL CONSIDERATIONS

### 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.  
Waste is classified as hazardous waste.

Waste from residues: EWC-code: 16 05 07

---

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	11/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 14: TRANSPORT INFORMATION

The product is covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

### 14.1. UN number

UN-No: 3089

### 14.2. UN proper shipping name

Proper Shipping Name: METAL POWDER, FLAMMABLE, N.O.S.

### 14.3. Transport hazard class(es)

Class: 4.1

### 14.4. Packing group

PG: II

### 14.5. Environmental hazards

Marine pollutant: No.

Environmentally Hazardous substance: Yes.

### 14.6. Special precautions for user

Special precautions: -

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk: -

## SECTION 15: REGULATORY INFORMATION

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulation: Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, with amendments.  
Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.  
The Control of Substances Hazardous to Health Regulations 2002 (S.I. 2002 No. 2677) with amendments.  
EH40/2005, Workplace exposure limits 2005, with amendments.  
The List of Wastes (England) (Amendment) Regulations 2005. (SI 2005 No. 895).

### 15.2. Chemical Safety Assessment

CSA status: No chemical safety assessment has been carried out.

---

# SAFETY DATA SHEET

Product name:	nVent® ERICO® Cadweld® One Shot	Page:	12/12
Supersedes date:		Revision:	2020-01-13
SDS-ID:	CADWELD_PLUS_UK	Version number:	GB-EN/1.0

---

## SECTION 16: OTHER INFORMATION

The user must be instructed in the proper work procedure and be familiar with the contents of these instructions.

Abbreviations and acronyms used in the safety data sheet: PBT = Persistent, Bioaccumulative and Toxic.  
vPvB = very Persistent and very Bioaccumulative.  
CSA= Chemical Safety Assessment.  
LD50 = Lethal Dose 50%.

Additional information: Classification according to Regulation (EC) No. 1272/2008: Calculation method.  
Physical Hazards: Expert judgement.

### Wording of H-statements:

H228	Flammable solid.
H261	In contact with water releases flammable gases.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

---

The information on this data sheet represents our current data and is reliable provided that the product is used under the prescribed conditions and in accordance with the application specified on the packaging and/or in the technical guidance literature. Any other use of the product which involves using the product in combination with any other product or any other process is the responsibility of the user.

---