


# MFZ

## nVent CADDY Macrofix Plus Non-Insulated M8/ M10

Part Number	Article Number	Pipe Range	Rod Size	Wrench size for M8/M10	Wrench size for M6 screw	Tightening torque for M6 screw	RAL Product Load Rating *
MFZ019	586801	15– 19 mm, 10 DN	M8/M10	13mm	10mm	2 Nm	1,000 N
MFZ023	586802	19 - 23 mm, 15 DN					
MFZ029	586803	23 – 29 mm, 20 DN					
MFZ035	586804	29 - 35 mm, 25 DN					
MFZ041	586805	35 – 41 mm					
MFZ048	586806	41 – 48 mm, 32 DN					1,500 N
MFZ055	586807	49 – 55 mm, 40 DN					
MFZ062	586808	54 - 62 mm, 50 DN					2,000 N
MFZ072	586809	62 – 72 mm					
MFZ083	586810	73 - 83 mm, 65 DN					2,500 N
MFZ093	586811	83 - 93mm, 80 DN					
MFZ103	586812	93 - 103mm, 90 DN					3,000 N
MFZ113	586813	103 – 113mm					
MFZ123	586814	113 - 123mm, 100 DN					3,200 N
MFZ133	586815	123 - 133mm					
MFZ143	586816	133 - 143mm, 125 DN					3,600 N
MFZ153	586817	143 - 153					
MFZ165	586818	155 - 165					
MFZ175	586819	165 - 175, 150 DN					
MFZ205	586820	195 - 205					
MFZ220	586821	210 - 220, 200 DN					

\* RAL Product Load Rating per RAL-GZ 655.



#### WARNING:

- nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at [www.nVent.com](http://www.nVent.com) and from your nVent customer service representative.
- nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
- All instructions must be completely followed to ensure proper and safe installation and performance.
- Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
- Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
- All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- Conformance to all governing codes.
- The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- Using appropriate industry standard hardware as noted above.

#### SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

TECHNICAL SUPPORT:  
[www.nVent.com](http://www.nVent.com)

CFS578\_A

1 OF 2

© 2020 nVent All Rights Reserved



