


PARTS LIST

Model SBG150

ITEM	PART No.	QTY	DESCRIPTION
✕	SBG150	✕	GRINDER ASSY, RAIL, PORTABLE, EFCO 940 ENGINE
1	A928P001	1	NUT, LOCK, BEARING, NL-02
2	A930U008	2	BEARING, BALL, SPINDLE, 42x20x12mm
3	A932C010	2	RING, SNAP, EXTERNAL, 2in
4	A932B044	1	RING, SPIRAL, INTERNAL, 42mm
5	A932C009	2	RING, SNAP, EXTERNAL, 25/32in
6	A930X012	1	PIN, RELEASE, QUICK, 3/16 x 3in
7	B3394	1	ENGINE, GRINDER, EFCO 940
8	SB013212	1	V-BELT, TY 3L240
9	C3097	1	SUPPORT, MAIN, ALUMINUM
10	B3406	1	SHAFT, GRINDER, STEEL
11	B3399	1	PULLEY, DRIVE, ALUM. 3-7/8in, V-BELT GROOVE
12	B3398	1	DRUM, CLUTCH
13	B3400	1	SPACER, CLUTCH DRUM
14	B3407	1	SUPPORT TUBE, SHAFT
15	SBG15002	1	GUARD, GRINDER, SIDE PULLEY, ALUMINUM
16	B3408	1	GUARD, GRINDER, FRONT PULLEY
17	A930U007	1	BEARING, NEEDLE, 14mm x 10mm x 12mm
18	A927F006	5	BOLT, HEX, 1/4-20 x 3/4in, ZINC PLATED
19	A929B004	5	WASHER, LOCK, 1/4in, ZINC/CHROME FIN.
20	S2333P	1	WHEEL, GRINDING
21	B3368	2	SPACERS, WHEEL
22	A928C024	1	NUT, THIN, (JAM) 5/8-18 LH
23	A927B009	3	SCREW, BUTTON, 1/4-20 x 3/4in
24	A928B001	3	NUT, HEX, NY-LOC, 1/4-20in
25	A927F024	1	BOLT, HEX, 5/16-18 x 1-1/4in, PLATED
26	A928B021	1	NUT, HEX, NY-LOC, 5/16-18, PLATED
27	B3367	1	GUARD, GRINDING WHEEL
28	B3365	1	GUARD, SLIDE COVER, GRINDING WHEEL
29	A927A011	3	SCREWS, BINDING HEAD
30	S3899	1	SLEEVE, HARD AL
31	B3387LH	1	BRACKET, LEFT HAND, AUX. HANDLE
32	B3387RH	1	BRACKET, RIGHT HAND, AUX. HANDLE
33	B3361	1	HANDLE, ROUND, STL
34	B3361A	1	GRIP, FOAM, 5in, BLACK
35	A927F022	2	BOLT, HEX, 5/16-18 x 3/4in, GRADE 5, ZINC/CHROME FIN.
36	A929B005	2	WASHER, LOCK, 5/16in, ZINC/CHROME FIN.
37	B3410	1	SUPPORT REST, STAND-OFF
38	B3390	2	NUT, SPECIAL SLANGE, M8-1.25
39	A930H039	1	PIN, DOWEL, 3/16 x 3/4in, STL

EXPLODED VIEW



TORQUE SCHEDULE

SBG150

ITEM NO.	TORQUE (INCH-LBS.)
1	100
18,35	30
22	100
23	100
25	80
29	20
38	130
EFCO ENGINE CLUTCH	190