














Floor standing enclosures 3R Combinable version

MOUNTING INSTRUCTIONS








WARNING: When mounting on or over a combustible surface, a floor plate of at least 1.43 mm galvanized or 1.6 mm uncoated steel extended at least 150 mm beyond the equipment on all sides must be installed.






WARNING: In order to maintain the environmental integrity of the enclosure, devices with the same environmental ratings shall be used to close openings in customized enclosure.

MCS-3R









H	A	B	C
1100	175	275	425
1400	325	325	525
1600	425	425	525
1800	525	525	525
2000	625	625	525
2200	725	625	725








Ref.	Pic.	Qty.
A		2
B		4











Metal Guider






MOUNTING THE LIFT HANDLE







Torque
4-5.5 Nm

A














Standard Locking System




Lift Handle Locking System



Standard Locking System



Lift Handle Locking System






NOTE: transparent covers are ordered separately



TOP PANEL

Ref.	Pic.	D (mm)	<800	≥800
A	M6x12		2	4
B	M12x20		4	4
C	M12		4	4








* - Used on enclosures 800mm deep and above.

** - Torque value for first tightening. For following tightening, torque value recommended is 4-5 Nm.


BACK PANEL



Ref.	Pic.	W (mm)	<1000	≥1000
A		M5x10	-	2
B		M6x12	16	18
C		M6	-	2



Torque
4-5 Nm







H	A	B
1100	-	350
1400	325	375
1600	425	475
1800	525	575
2000	625	675
2200	725	775

* - Used on enclosures 1000mm wide and above.

MOUNTING BOTTOM PLATES






Ref.	Pic.	Qty.
A	St. 5.5x10	6/8
B		5/7





SEALING BOTTOM PLATES

Required for IP55




Ref.	Pic.	Qty.
A	 4,5x8	6m
B	 25x25	1,6m
C		4

BG01 ordered separately








MOUNTING PLATE





Ref.	Pic.	Qty.
A		2
B		2
C		2
D		1
E		1
F		1
G		1



MOUNTING





UNMOUNTING











MPD02





Ref.	Pic.	Qty.
A	M5X12	2
B	Bottom left	1
C	Bottom right	1



MOUNTING



UNMOUNTING











SPM-3R




Ref.	Pic.	Qty.
A		6/8/9
B		6/8/9
C		2
D		1
E		1
F		1
G		

Side panel mounting





* Top middle fixation (for 900 mm depth and above)


Alternative 1



Alternative 2




** Bottom middle fixation (for 900 mm depth and above)





SPM-3R



Retainer mounting









NOTE: For the old design frame (from 700 mm till 800 mm depth), the following additional steps are required:





CCI06

Ref.	Pic.	Qty.
A		8
B		6
C		12
D		6

















CCM 04

Ref.	Pic.	Qty.
A		4
B		8

MOUNTING







Note: It is mandatory for all four brackets to be installed at all four corners !





* The fixation holes can be used to better fix the bracket to the frame, using cage nuts and screws !












Ref.	Pic.	Qty.
A		4
B		4
C		2
D		4





MPF

Ref.	Pic.	Qty.
A		1
B		1
C		2
D		2




Back view





CNM

Ref.	Pic.	Qty.
A		1

